




Disposable Trocar



Advantages of KANGJI trocar:

- Can achieve visual puncturing under the guidance of 0° endoscope to avoid harm caused by blind inserting
- With multi-seal system and no need to use reducer when using different surgical instruments in order for improving surgery efficiency
- Detachable design for taking specimen conveniently
- Threaded cannula for effectively increasing the friction between cannula and abdominal wall, to avoid the cannula dropping off
- Particular bladeless tip design to avoid damaging the tissue on the premise of sharp puncturing
- Using medical polymer materials for easy operating
- Single use for preventing cross-infection

Reusable metal trocar should be cleaned like this to finish cleaning thoroughly, You did it?



The actual cost of reusable metal trocar contains below: You found it?



The clinical advantage of disposable trocar of Kangji Medical

- ✓ To ensure the sharpness of obturator, to avoid sharpness declination of cutting edge of reusable trocar after cleaning and sterilization.
- ✓ To ensure that each product has a good sealing performance, to avoid sealing performance degradation after cleaning and disinfection for many times.
- ✓ Single patient use, to avoid cross-contamination and cross-infection.
- ✓ Eliminate the cumbersome and high risk of cleaning, disinfection work of reusable trocar and reduce hospital manpower expenditure.
- ✓ Easy operation to reduce misuse and unnecessary damage.
- ✓ To reduce the incidence of puncture hole hernia, spurs and other complications.

Less fascia injury
The incision caused by disposable trocar of Kangji Medical is obviously smaller than traditional triangular pyramid or bladed trocar.

Kangji trocar	Triangular pyramid trocar	Bladed trocar

Faster tissue reset
The wound caused by disposable trocar of Kangji Medical is symmetrical, narrow and tight. After removal of the trocar cannula, the tissue will be reset immediately.

Kangji trocar	Triangular pyramid trocar	Bladed trocar



■ Threaded design



■ Optical tip



■ Universal seal

Detachable housing

